



RF-LLX-CL 7/8" SHF1

Radiation

50Ω

SHF1, UV

DNV


Application

Radial coaxial/antenna cable for ships, buildings and tunnels where reception conditions for radio signals are weak. RF-LLX-CL is used where requirements for a large frequency range are required.



Construction coaxial

Conductor	Smooth Cu-tube $\varnothing = 9.0 \pm 0.2$ [mm]
Dielectric	Foamed PE $\varnothing = 22.0 \pm 0.5$ [mm]
Screen	Corrugated slotted Cu-tube $\varnothing = 24.9 \pm 0.5$ [mm]
Jacket	Black or grey SHF1 UV-resistant
Outer diam.	28.0 ± 0.5 [mm]
Weight	456 [kg/km]
Jacket marking	NEK Kabel – RF-LLX-CL 7/8" 50 – SHF1 – DD.MM.YYYY – ****m



Specifications Coax

Temperature range	-25 – +70 [°C]
Impedance	50 [Ω]
Insulation resistance	10000 [MΩ/km]
Velocity factor	88 [%]
Max pulling force	1500 [N]
Min bending radius installed	140 [mm]
Min. bending flexible	250 [mm]
Identification of radiation:	Opposite side of the slots



Norms

Halogenfree, max content corrosive and toxic gases	IEC 60754-1 & IEC 60754-2
Material properties, insulation and sheath	IEC 60092-360 (359) 3582
Design and testing standards	IEC 60096-0-1 Ed 3 EN 50288-1
Flame resistance	IEC 60332-3-22 Cat.A
Flame retardant	IEC 60332-1-2
Weather resistant	ASTM G 154
Smoke emission	IEC 61034-2
Oil and fuel resistant	IEC 60811-2-1 Mineral Oils, IRM 902: 23°C / 7 days, 70°C / 4h Diesel, IRM 903: 23°C / 7 days, 70°C / 4h
UV-resistant	ASTM G 154
CPR classification	Dca-s1,d2,a1
Certification	DNV

Part No.	1092480
----------	---------



NEK offers connectors for RF-LLX-CL 7/8" 50:
Female part no. 65444

Attenuation

Frequency [MHz]	Attenuation [dB/100m ±5%]	Coupling loss 95% [dB±10]
150	≤ 1.8	70
450	≤ 3.6	74
700	≤ 4.2	77
900	≤ 5.3	79
1800	≤ 7.6	78
2200	≤ 8.6	77
2400	≤ 9.0	84



VSWR

Frequency [MHz]	-
260 – 480	≤ 1.25
820 – 960	≤ 1.25
1700 – 1860	≤ 1.25
1900 – 2050	≤ 1.30
2100 – 2200	≤ 1.30
2300 – 2400	≤ 1.30

Updated

Date	Rev.	Description
21.10.2019	1	O.diam. and coupling loss
15.05.2020	2	VSWR
17.02.2022	3	Coupling loss
23.11.2023	4	Additional info
23.04.2025	5	Attenuation and CPR